



**de** Montageanleitung  
 \*) Über Kundendienst erhältlich  
**en** Installation instructions  
 \*) Available from customer service  
**fr** Notice de montage  
 \*) Disponible par le biais du service après-vente  
**nl** Montagevoorschrift  
 \*) Tegen meerprijs bij de Servicecentrum verkrijgbaar  
**it** Istruzioni per il montaggio  
 \*) Disponibile presso il servizio assistenza clienti  
**el** Οδηγός τοποθέτησης  
 \*) Διαθέσιμα από την υπηρεσία τεχνικής εξυπηρέτησης πελατών

**es** Instrucciones de montaje  
 \*) Se puede adquirir a través del Servicio de Asistencia Técnica Oficial de la marca  
**pt** Instruções de montagem  
 \*) Pode ser adquirido nos nossos Serviços Técnicos  
**sv** Monteringsanvisning  
 \*) Kan fås via Service  
**de** Monteringsanvisning  
 \*) fåes hos kundeservice  
**fi** Asennusohje  
 \*) Saatavissa huoltopalvelusta  
**da** Monteringsvejledning  
 \*) Kan købes hos serviceafdelingen

**tr** Montaj kılavuzu  
 \*) Yetkili servis üzerinden alınabilir  
**ru** Инструкция по монтажу  
 \*) Можно получить в сервисном центре  
**sk** Montážni návod  
 \*) K dispozícii prostredníctvom servisnej služby  
**pl** Instrukcja montażu  
 \*) Do uzyskania w punkcie serwisowym  
**hu** Szerelési utasítás  
 \*) A vevőszolgálaton keresztül kapható:  
**hr** Uputa za montažu  
 \*) može dobiti kod službe održavanja

**mk** Упатство за монтажа  
 \*) се добива преку службата за купувачи  
**sl** Navodilo za montažo  
 \*) Lahko nabavite v servisni službi  
**cs** Uputstvo za montažu  
 \*) Može se nabaviti preko servisne službe  
**et** Monteerimisjuhend  
 \*) Kõige klientiteeninduselt  
**lt** Montavimo instrukcija  
 \*) Ja galima gauti klientų aptarnavimo servise  
**lv** Montāžas pamācība  
 \*) Var saņemt servisa dienestā

**sk** Návod na montáž  
 \*) Dostanete v službe zákazníkom  
**scj** Udružes për montim  
 \*) Sigurohet nëpërmjet servisit  
**bs** Uputa za montažu  
 \*) Može se dobiti preko servisne službe  
**fa** راهنمای مونتاژ  
 \*) از مرکز خدمات پس از فروش تهیه فرمایید  
**ar** تعليمات التركيب  
 \*) يمكن طلبها من مراكز خدمة العملاء  
**ko** 설치 설명서  
 \*) 고객센터 센터에서 구입 가능

**zh** 安装说明书  
 \*) 可向售后服务站索取。  
**uk** Інструкція з монтажу  
 \*) Можна отримати через сервісну службу  
**ro** Instrucțiune de montaj  
 \*) disponibilă la serviciul pentru clienți  
**id** Instruksi Pemasangan  
 \*) bisa didapatkan melalui Customer Service  
**ky** сже қосу туралы нұсқаулар!  
 \*) Сервис қызметі меркенту орталығында алуға жағдайы

640 Integr. Niro-Leisten - 81,5 cm - m. GS 9001 043 217 (9410)

**1** Preparation of the cabinet opening. Dimensions: 815 mm, 550 mm, 600 mm (max. 606 mm), 575 mm, 100-50 mm.

**2** Installation of the top panel. Part 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**3** Mounting the top panel. Dimensions: 815-875 mm, 575 mm, 600 mm (max. 606 mm), 100-50 mm.

**4a** Mounting the top panel. Dimensions: 600 mm (max. 606 mm), 600 mm.

**4b** Mounting the top panel. Dimensions: 600 mm.

**5** Mounting the top panel. Dimensions: 566 mm, ~12 mm, Ø 2 mm.

**6** Mounting the top panel. Dimensions: 0-60 mm, SW 10, SW 13.

**7** Mounting the top panel. Dimensions: max. 725 mm, max. 167 mm, 594 mm.

**8** Mounting the top panel. Dimensions: max. 1.2 mm, 2.5-8.5 kg.

**9** Mounting the top panel. Dimensions: 12-11 mm, 12-20 mm, 21-29 mm, 30-39 mm, 63-68 mm. Mat-Nr. 674259, Mat-Nr. 674253.

**10** Mounting the top panel. Dimensions: 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**11** Mounting the top panel. Dimensions: 2.5 - 8.5 kg.

**12** Mounting the top panel. Dimensions: X, X.

**13** Mounting the top panel. Dimensions: 25, 26, 27, 28, 29, 30, 31.

**14** Mounting the top panel. Dimensions: 502 mm, ~12 mm, Ø 2 mm.

**15** Mounting the top panel. Dimensions: 0.38 mm, min. 280 mm, max. 1.1 m, 28, 29, 30, 31. max. 10 Nm. 0.05 - 1 MPa (0.5 - 10 bar) max. 60°C.

**16** Mounting the top panel. Dimensions: 3 m, 3 m, 2.2 m, 2 m, 0.22 mm, 2.2 m, Mat-Nr. 350564, Mat-Nr. 644533, Mat-Nr. 644534.

**17** Mounting the top panel. Dimensions: 45, 45.

**18** Mounting the top panel. Dimensions: 18.

**19** Mounting the top panel. Dimensions: 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**20** Mounting the top panel. Dimensions: 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**21** Mounting the top panel. Dimensions: 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**22** Mounting the top panel. Dimensions: 22, 23, 24, 25, 26, 27, 28, 29, 30, 31.

**23** Mounting the top panel. Dimensions: 23, 24, 25, 26, 27, 28, 29, 30, 31.

**24** Mounting the top panel. Dimensions: 24, 25, 26, 27, 28, 29, 30, 31.

**25** Mounting the top panel. Dimensions: 25, 26, 27, 28, 29, 30, 31.

**26** Mounting the top panel. Dimensions: 26, 27, 28, 29, 30, 31.

**27** Mounting the top panel. Dimensions: 27, 28, 29, 30, 31.

**28** Mounting the top panel. Dimensions: 28, 29, 30, 31.

**29** Mounting the top panel. Dimensions: 29, 30, 31.

**30** Mounting the top panel. Dimensions: 30, 31.

**31** Mounting the top panel. Dimensions: 31.

